



2 . Voltage/ Current / Sound Pressure





3 . Dimensions and Material

3-1 Shape



Unit : mm

3-2 Material

Housing	PPO plastic resin (Color : Black)
Leading Pin	Tin Plated Brass
Weight (Gram)	1.8

HITPOINT TEL:8862-26013311 FAX:8862-26013898 NO.4 Lane 505, Zhongzheng Rd, Linkou Shiang, Taipei, Taiwan 24445 . R.O.C **4. TESTING METHOD** Standard Measurement conditions *Temperature:25<u>+</u>2* °C *Humidity:45-60%* Acoustic Characteristics The oscillation frequency, current consumption and sound pressure are measured by the measuring instruments shown below. 10cm FUNCTION AMPERE SOUNDER **MICROPHONE** dB METER GENERATOR METER In the measuring test, buzzers is placed as follows: SAMPLE MICROPHONE 10CM

HITPOINT TEL:8862-26013311 FAX:8862-26013898 NO.4 Lane 505, Zhongzheng Rd,. Linkou Shiang, Taipei, Taiwan 24445 . R.O.C

5. RELIABILITY

ITEMS	METHOD OF TEST AND MEASUREMENTS	PERFORMANCE
Coldness	After 98 hours of being exposed to -30 $^{\circ}\!C$	No abnormality
withstanding	environment, should be returned to normal	shall exist
	environment for 2 hours, then re-proceed to test.	
Hotness	After 98 hours of being exposed to +80 ${}^{\circ}\!{}^{\circ}\!{}^{\circ}$	No abnormality
withstanding	environment, should be returned to normal	shall exist
	environment for 2 hours, then re-proceed to test.	
Humidity	After 98 hours of being exposed to 40 ${}^\circ\!\!{}^\circ$ 95%RH	No abnormality
withstanding	environment in actual operation, should be	shall exist
	returned to normal environment for 2 hours, then	
	re-proceed to test.	
Durability	Testing after 1,000 hours actual continuous	No abnormality
	operation. (at standard measurement conditions)	shall exist
Drop	A natural drop from 75cm high down to the	No abnormality
withstanding	ground.	shall exist
Vibration	Vibration of 2,000 cycles per minute, 2mm	No abnormality
withstanding	amplitude, applied in X, Y and Z directions for 30	shall exist
	minutes each.	

6. PACKAGE METHOD

- <1> 100pcs per box, Total 10 boxes per carton, total 1000pcs carton; Volume: L*W*H=510*330*300mm
- < 2 > RoHS Mark

